



Carrier Kill with Universal viaDNA Remote – Black Box


Select the spooky2 software **Settings** tab




In the **Signal Settings** box ... type in the **Amplitude** and **Offset** numbers for **Out1** and **Out2**



In the **Output Control** box ... select **Out1 fixed at ...** type in **2977792**



In the **Waveform Setup** box ... select **Sine Waveform** for **1** and **2**



Carrier Kill with Universal viaDNA Remote – Black Box

The oscilloscope box (right hand side of Settings window) should look like this

